

# Product datasheet

Specifications



## 1 Gang Blank Plate

KB30\_WE

### Main

Range	Vivace
Product or component type	Blank plate
Device short name	KB30

### Complementary

Number of gangs	1 gang
Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround
Projecting depth	8 mm
Device mounting	Flush
Width	86 mm
Height	86 mm

### Environment

Standards	BS 5733
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	57.767 g
Package 1 Height	3.1 cm
Package 1 Width	8.6 cm
Package 1 Length	25.3 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	15
Package 2 Weight	1.032 kg

Package 2 Height	15.0 cm
Package 2 Width	38.0 cm
Package 2 Length	15.0 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	150
Package 3 Weight	8915.0 g
Package 3 Height	210.0 mm
Package 3 Width	315.0 mm
Package 3 Length	500.0 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Recommended replacement(s)