

# Product datasheet

Specifications



## 115/240V Shaver Unit

KBT727V\_WE

### Main

Range	Vivace
Product or component type	Shaver socket
Device short name	KBT
Device application	Power supply
Device presentation	Complete mechanism

### Complementary

Number of gangs	2 gangs
Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	120.6 mm
Embedding depth	47 mm
Input voltage	240 V AC
Output voltage	115 V AC
Network frequency	50 Hz
Connections - terminals	Pillar terminal
Terminal identifier	L N E
Tightening torque	0.4 N.m
Clamping connection capacity	2.5 mm <sup>2</sup>
Width	146 mm
Height	86 mm

### Environment

Standards	IEC 61558-2-5
-----------	---------------

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
IP degree of protection	IP21

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	4.9 cm
Package 1 Length	14.6 cm
Package 1 Weight	671.5 g
Unit Type of Package 2	BB1
Number of Units in Package 2	2
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	2 cm
Package 2 Weight	1.413 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	20
Package 3 Height	31.5 cm
Package 3 Width	50 cm
Package 3 Length	50 cm
Package 3 Weight	13680 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Recommended replacement(s)