# **Product datasheet**

Specifications





# mini Pragma surface enclosure - 1 x 12 modules - translucid door

MIP12112T

#### Main

Range	Resi9
Product Name	Resi9 MP
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	12
Nb Of Horizontal Rows	1
Type Of Door	Translucid
Width	268 mm outside:
Height	228 mm outside:
Depth	101.5 mm outside:

### Complementary

Enclosure Mounting	Surface
9 Mm Pitches	24
Total Number Of 18 Mm Modules	12
[In] Rated Current	63 A
Type Of Rail	35 mm asymmetrical rail
Mounting Plate Description	Without mounting plate
Cable Entry	1 trunking flange 1 bare flange
Terminal Block Function	Earth / neutral
Number Of Terminal Blocks	1 earth (screwed) with 8 outgoers 1 neutral (screwed) with 8 outgoers
Distribution Block Outgoers	1 x 16 mm <sup>2</sup> for earth 1 x 16 mm <sup>2</sup> for neutral 3 x 6 mm <sup>2</sup> for earth 3 x 6 mm <sup>2</sup> for neutral 4 x 10 mm <sup>2</sup> for neutral 4 x 10 mm <sup>2</sup> for neutral
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Internal Depth	80 mm
Colour	Front face: white (RAL 9003) Door: translucid
Market Segment	Small commercial Residential

### Environment

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality Labels	IMQ
Fire Resistance	Door: 650 °C Back part: 650 °C Front face: 650 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-2560 °C

## **Packing Units**

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.000 cm
Package 1 Width	22.500 cm
Package 1 Length	27.000 cm
Package 1 Weight	804.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	8
Package 2 Height	30.000 cm
Package 2 Width	41.000 cm
Package 2 Length	53.000 cm
Package 2 Weight	7.309 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	128
Package 3 Height	120.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	128.944 kg

### **Contractual warranty**

Warranty

12 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations