


Product datasheet

Specifications



Metal extension box H300xW300xD80 IP66 IK10 RAL 7035

NSYAES338SB

! Discontinued

! Discontinued on: Sep 9, 2020

! End-of-service on: Nov 18, 2020

Main

Range	Spacial
Product Name	Spacial SBM
Device Application	Multi-purpose
Category	Extension box
Device Short Name	SBM
Enclosure Nominal Height	300 mm
Enclosure Nominal Width	300 mm
Enclosure Nominal Depth	80 mm
Device Composition	1 body 4 screw
Body Type	Single piece body folded and welded
Cover Fixing	Half turn metal screw
Lock Type	Captive screw PZ2 inside the enclosure

Complementary

Material	Sheet steel
Surface Finish	Polyester powder
Colour	Grey (RAL 7035)
Ip Degree Of Protection	IP66 1 device conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ambient Air Temperature For Storage	-35...60 °C
Operating Temperature	-35...80 °C
Net Weight	1.972 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)