Product datasheet

Specifications

Green Premium[™]



Climasys Ultra thin resistance heater low starting current 12W 240V 110x140mm

NSYCRS10W240V

Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Ultra thin resistance heater
Power Range	12 W
Input Voltage	240 V AC 50/60 Hz
Electrical Connection	Cable length: 2 m

Complementary

oompromental y	
Operating Position	Vertical Horizontal
Ambient Air Temperature For Operation	-6070 °C
Temperature Setting Range	-4070 °C
Material	Silicone rubber
Height	110 mm external:
Width	140 mm external:
Depth	1.6 mm external:
Device Composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts fixing accessories
Condition Of Use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing Mode	By 4 screws
Mounting Support	Standard mounting plate Adhesive Velcro DIN rail Telequick mounting plate

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	25.5 cm
Package 1 Length	28.5 cm

Package 1 Weight	280.0 g
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	440
Package 2 Height	172.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	137.0 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations