

# Product datasheet

Specifications



## Fluorescent compact lamp, 11W, 120V 50/60Hz, american socket (UL-CSA)

NSYLAMCU

⚠ Discontinued on: Sep 9, 2020

⚠ Discontinued

### Main

|                                    |                                                    |
|------------------------------------|----------------------------------------------------|
| Range Of Product                   | Lighting and power sockets                         |
| Accessory / Separate Part Category | Lighting accessory                                 |
| Product Or Component Type          | Lamp                                               |
| Device Application                 | Multi-purpose                                      |
| Device Composition                 | fixing elements<br>lamp<br>switch and power socket |

### Complementary

|                                |                                                                                                                                                                                        |
|--------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Outlet Standard                | American                                                                                                                                                                               |
| Rated Lamp Wattage             | 11 W                                                                                                                                                                                   |
| [Ue] Rated Operational Voltage | 120 V 50/60 Hz                                                                                                                                                                         |
| Bulb Base                      | 2G7                                                                                                                                                                                    |
| Bulb Type                      | Fluorescent                                                                                                                                                                            |
| Control Type                   | Built-it switch                                                                                                                                                                        |
| Luminous Flux                  | 900 lm                                                                                                                                                                                 |
| Service Life In Hours          | 8000 h                                                                                                                                                                                 |
| Electrical Connection          | Screw connector <= 2.5 mm²                                                                                                                                                             |
| Mounting Location              | Top front of enclosure                                                                                                                                                                 |
| Mounting Support               | Cross rails<br>Upright<br>Metal parts<br>DIN rail                                                                                                                                      |
| Fixing Mode                    | Screws<br>Magnetic fixing<br>Clip-in                                                                                                                                                   |
| Range Compatibility            | Spacial Spacial S3D<br>Spacial Spacial CRN<br>Thalassa Thalassa PLA<br>Thalassa Thalassa PLM<br>Spacial Spacial SFX<br>Spacial Spacial SMX<br>Spacial Spacial SF<br>Spacial Spacial SM |
| Material                       | Light grey plastic                                                                                                                                                                     |
| Height                         | 40 mm                                                                                                                                                                                  |
| Width                          | 372 mm                                                                                                                                                                                 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|       |       |
|-------|-------|
| Depth | 63 mm |
|-------|-------|

## Environment

|                                       |                                                                           |
|---------------------------------------|---------------------------------------------------------------------------|
| Ip Degree Of Protection               | IP20 conforming to IEC 60529                                              |
| Electrical Insulation Class           | Class I                                                                   |
| Flame Retardance                      | V0 conforming to UL 94                                                    |
| Electromagnetic Compatibility         | Emission standard for industrial environments conforming to IEC 61000-6-4 |
| Standards                             | UL 508 A                                                                  |
| Product Certifications                | UL                                                                        |
| Ambient Air Temperature For Operation | -16...65 °C                                                               |
| Ambient Air Temperature For Storage   | -40...70 °C                                                               |

## Packing Units

|                              |     |
|------------------------------|-----|
| Unit Type Of Package 1       | PCE |
| Number Of Units In Package 1 | 1   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|