



reversible internal door polyester 2 locks grid pattern forPLM108

NSYPAP108G

Main

Range	Thalassa
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Front side
Range Compatibility	Thalassa Thalassa PLM
Device Composition	1 door 1 handle 4 fixing brackets

Complementary

Material	Polyester charged with fibreglass	
Colour	Grey (RAL 7035)	
Lock Type	Lock 5 mm double bar	
Number Of Locks	2	
Door Type	Internal plain	
Door Opening Side	Reversible (110 °)	
Height	Grid pattern: 850 mm	
Width	Grid pattern: 650 mm	
Depth	37 mm available depth between enclosure door: 269 mm available depth between rear:	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	79.000 cm
Package 1 Length	99.000 cm
Package 1 Weight	2.741 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	29.000 cm

Package 2 Width	90.000 cm
Package 2 Length	100.000 cm
Package 2 Weight	14.021 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	30
Package 3 Height	135.000 cm
Package 3 Width	100.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	97.126 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations