



Metal industrial box plain door H150xW400xD80 IP66 IK10 RAL 7035

NSYSBM15408

Main

| Range | Spacial | |
|--------------------------------|---------------------------------------|--|
| Product Name | Spacial SBM | |
| Device Application | Multi-purpose | |
| Category | Industrial box | |
| Device Short Name | SBM | |
| Enclosure Type | Flat face box | |
| Enclosure Nominal Height | 150 mm | |
| Enclosure Nominal Width | 400 mm | |
| Enclosure Nominal Depth | 80 mm | |
| Enclosure Mounting | Wall mounted | |
| Device Composition | 4 cover screw 1 cover 1 body | |
| Body Type | Single piece body folded and welded | |
| Type Of Front Cover | Plain door | |
| Cover Fixing | Half turn metal screw | |
| Lock Type | Captive screw PZ2 outside sealed area | |
| Removable Parts | Cover by captive screws | |

Complementary

| Material | Sheet steel | |
|-------------------------------------|------------------------------|--|
| Surface Finish | Polyester powder | |
| Colour | Grey (RAL 7035) | |
| Standards | IEC 62208 | |
| Product Certifications | LR DNV-GL UL BV | |
| Ip Degree Of Protection | IP66 conforming to IEC 60529 | |
| Ik Degree Of Protection | IK10 conforming to IEC 62262 | |
| Ambient Air Temperature For Storage | -3560 °C | |
| Operating Temperature | -3580 °C | |
| Net Weight | 2.15 kg | |

Packing Units

| 9 | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 10.0 cm |
| Package 1 Width | 17.0 cm |
| Package 1 Length | 42.0 cm |
| Package 1 Weight | 2.15 kg |
| Unit Type Of Package 2 | P12 |
| Number Of Units In Package 2 | 108 |
| Package 2 Height | 171.0 cm |
| Package 2 Width | 80.0 cm |
| Package 2 Length | 120.0 cm |
| Package 2 Weight | 245.0 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| Ø | Toxic Heavy Metal Free | |
| ② | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |