Product datasheet

Specification





ABS box IP66 IK07 RAL7035 Int.H105W65D55 Ext.H116W74D62 Opaque cover H10

NSYTBS1176

Main

Range	Thalassa	
Product Name	Thalassa TBS	
Device Application	e Application Multi-purpose	
Category	Industrial box	
Height	116 mm	
Width	74 mm	
Depth	62 mm	
Internal Height	105 mm	
Internal Width	65 mm	
Internal Depth	55 mm	
Enclosure Mounting	Wall mounted	
Device Composition	1 body 1 cover 4 cover screw	
Quantity Per Set	Set of 5	
Body Type	One piece moulded	
Type Of Front Cover	Low plain cover	
Cover Fixing	Metal screws	
Lock Type	Captive screw flat outside sealed area	
Removable Parts	Cover by captive screws	

Complementary

,		
Material	ABS (acrylonitrile butadiene-styrene)	
Colour	Grey (RAL 7035)	
Standards	IEC 62208	
Product Certifications	TÜV	
Electrical Insulation Class	Class II	
Ip Degree Of Protection	IP66 conforming to NEMA 4.4X	
Ik Degree Of Protection	IK07 conforming to IEC 62262	
Glow Wire Resistance	650 °C conforming to IEC 60695-2-11	
Ambient Air Temperature For Storage	-1540 °C	
Operating Temperature	-2560 °C	

Net Weight 0.108 kg

Packing Units

· · · · · · · · · · · · · · · · · · ·	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	7.4 cm
Package 1 Length	11.5 cm
Package 1 Weight	92 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	8.8 cm
Package 2 Width	12.6 cm
Package 2 Length	33.4 cm
Package 2 Weight	532 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	105
Package 3 Height	40.6 cm
Package 3 Width	40.2 cm
Package 3 Length	61.4 cm
Package 3 Weight	12.168 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations