
Product datasheet

Specifications



() Discontinued

PratiKa wander plug straight - 32 A - 3P + E -200...250 V AC - IP44

PKE32M424

() Discontinued on: Aug 27, 2020

(!) End-of-service on: Jun 30, 2023

Main

| Range | PratiKa |
|---------------------------|--------------|
| Product Or Component Type | Wander plug |
| Device Short Name | PratiKa plug |
| Plug, Socket Category | Low voltage |
| Poles Description | 3P + E |
| Network Type | AC |
| Outlet Standard | Industrial |

Complementary

| oompicinentary | |
|--|---|
| Plug, Socket, Control Station Shape | Straight |
| [In] Rated Current | 32 A |
| [Ue] Rated Operational Voltage | 200250 V |
| Network Frequency | 50/60 Hz |
| Ground Lug Clockwise Position | 9 h |
| Plug, Socket Material | Housing: self-extinguishing engineering polymer |
| Contacts Material | Sleeves: brass |
| Connections - Terminals | Captive screws |
| Cable Cross Section | 2.510 mm ² |
| Cable Outer Diameter | 11.521 mm |
| Cable Entry | Fair lead Cable gland |
| Thread Type | Pg 21 |
| Net Weight | 0.2 kg |
| Height | 152 mm |
| Width | 76 mm |
| Depth | 76 mm |
| Colour | Grey (RAL 7035) |
| Voltage Colour | Blue |

Environment

| Standards | IEC 60309-2 IEC 60309-1 |
|--|---|
| Ip Degree Of Protection | IP44 conforming to IEC 60529 |
| Ik Degree Of Protection | IK08 conforming to EN 62262 |
| Fire Resistance | 850 °C conforming to IEC 60695-2-11 |
| Relative Humidity | 50 % at 40 °C 70 % at 30 °C 90 % at 20 °C |
| Operating Altitude | 2000 m |
| Ambient Air Temperature For Operation | 35 °C(86400 s) -2540 °C |

Packing Units

| • | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 16.0 cm |
| Package 1 Width | 6.0 cm |
| Package 1 Length | 7.0 cm |
| Package 1 Weight | 224.0 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 12.0 cm |
| Package 2 Width | 27.0 cm |
| Package 2 Length | 27.0 cm |
| Package 2 Weight | 2.397 kg |
| Unit Type Of Package 3 | S03 |
| Number Of Units In Package 3 | 30 |
| Package 3 Height | 30.0 cm |
| Package 3 Width | 30.0 cm |
| Package 3 Length | 40.0 cm |
| Package 3 Weight | 7.678 kg |
| | |

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|-----------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Circularity Profile | No need of specific recycling operations |