

Product datasheet

Specifications



WPS - 20A 500V - triple phase 5 pole - round pin - IP66 (grey)

S56SO520GY

Main

Range of product	WPS
Product or component type	Socket-outlet
Device short name	56 series
Outlet poles configuration	3P + N + E round pin
Rated current	20 A at 500 V AC
Number of gangs	1 gang

Complementary

Device mounting	Surface
Material	PVC (polyvinyl chloride) UV stabilised: back box
Colour tint	Light grey
Colour of cover	Transparent
Height	107 mm
Width	101 mm
Depth	104 mm

Environment

IP degree of protection	IP66
Standards	GB/T 11918:2001

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.2 cm
Package 1 Width	10.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	500.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Recommended replacement(s)