

# Product datasheet

Specifications



## CANopen SUB-D9 female connector - bended at 90° - IP20

TSXCANKCDF90T

### Main

Range Of Product	CANopen
Bus Type	CANopen
Accessory / Separate Part Category	Connection accessories
Accessory / Separate Part Type	Connector with line terminator
Ip Degree Of Protection	IP20
Accessory / Separate Part Destination	CANopen bus

### Complementary

Electrical Connection	1 female connector SUB-D 9 elbowed
Net Weight	0.046 kg

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.500 cm
Package 1 Width	9.400 cm
Package 1 Length	11.400 cm
Package 1 Weight	47.000 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	225
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	10.350 kg

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins