

# Product datasheet

Specifications



## Kavacha - 35A - 440V - Surface Mount Double Pole Isolating Switch - IP66

WHD35\_GY

### Main

Range	Kavacha
Product or component type	Isolating switch
Device short name	W
Device application	Control

### Complementary

[Ie] rated operational current	35 A at 440 V AC-22A
Poles description	2P
Motor Rating	M180
Width	82 mm
Height	170 mm
Depth	90 mm

### Environment

IP degree of protection	IP66
Standards	IEC 60947-3
Environmental characteristic	Weatherproof

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.3 cm
Package 1 Width	9 cm
Package 1 Length	8.3 cm
Package 1 Weight	1.6 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Height	36.5 cm
Package 2 Width	28.5 cm
Package 2 Length	43.5 cm

---

Package 2 Weight 17000 g

## Offer Sustainability

---

Sustainable offer status Green Premium product

---

REACH Regulation [REACH Declaration](#)

---

EU RoHS Directive Compliant  
[EU RoHS Declaration](#)

---

Mercury free Yes

---

China RoHS Regulation [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information

---

RoHS exemption information Yes

---

Environmental Disclosure [Product Environmental Profile](#)

Recommended replacement(s)