

Product datasheet

Specifications



Kavacha - 55A - 440V - Surface Mount triple Pole Isolating Switch - IP66

WHT55_GY

Main

Range	Kavacha
Product or component type	Isolating switch
Device short name	W
Device application	Control

Complementary

[Ie] rated operational current	55 A at 440 V AC-22A
Poles description	3P
Motor Rating	M160
Width	82 mm
Height	170 mm
Depth	90 mm

Environment

IP degree of protection	IP66
Standards	IEC 60947-3
Environmental characteristic	Weatherproof

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	733.333 g
Package 1 Height	17.5 cm
Package 1 Width	9 cm
Package 1 Length	8.3 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Weight	22000.0 g
Package 2 Height	36.5 cm
Package 2 Width	28.5 cm

Package 2 Length	43.5 cm
Unit Type of Package 3	P12
Number of Units in Package 3	540
Package 3 Weight	414000.0 g
Package 3 Height	130 cm
Package 3 Width	80 cm
Package 3 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)