



pilot light Ø8 - IP40/IP65 - red - covered LED included - 24V - faston

XVLA234

Main

Range Of Product	Harmony XVL		
Product Or Component Type	LED pilot light with integral lens cap		
Component Name	XVL		
Mounting Diameter	8 mm		
Light Source	Covered LED		
Light Block Colour	Red		
Protection Type	Built-in by diode Integral ballast resistor		
[Us] Rated Supply Voltage	24 V		
Ip Degree Of Protection	IP65 (with seal XVLZ911) conforming to IEC 60529 IP65 (with seal XVLZ911) conforming to NF C 20-010 IP40 conforming to IEC 60529 IP40 conforming to NF C 20-010		

Complementary

•	
Supply Circuit Type	DC
Connections - Terminals	Tag for Faston connectors: 2.8 x 0.5 mm Tag for soldering connectors
Current Consumption	18 mA
[Ui] Rated Insulation Voltage	50 V conforming to IEC 60947-1
Bulb Lifespan	100000 h
Nominal Voltage Limit	0.81.1 Un
Terminals Description Iso N°1	(X1-X2)PL
Height	10 mm
Width	10 mm
Depth	36 mm
Net Weight	0.003 kg

Environment

Product Certifications	CSA UL
Protective Treatment	TC
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4070 °C

Overvoltage Category	Class 3 conforming to IEC 60536
	Class 3 conforming to NF C 20-030

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	2 cm
Package 1 Length	4 cm
Package 1 Weight	3 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3 cm
Package 2 Width	10 cm
Package 2 Length	11 cm
Package 2 Weight	32 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm
Package 3 Weight	512 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes


Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	No need of specific recycling operations		

Dimensions Drawings

LED Pilot Light

Dimensions



- (1) Tags for Faston connectors or soldered connections
- e panel thickness: 1 to 8 mm/0.03 to 0.31 in.


С		Ø	
mm	in.	in. mm	
34	1.34	10	0.39

XVLA234

Mounting and Clearance

LED Pilot Light

Panel Drilling



Ø mi	Ø min		G min		H min	
mm	in.	mm	in.	mm	in.	
8.2	0.32	10.5	0.41	10.5	0.41	