



24V 70 W HALOGEN ROTATING BEACON(ORANGE)

XVR1B95

! Discontinued on: Aug 27, 2020

! Discontinued

Main

Range Of Product	Harmony XVR Application	
Product Or Component Type	Rotating mirror beacon	
Component Name	XVR	
Mounting Diameter	165 mm	
Light Source	Bulb included, orange	
Bulb Type	Halogen with H1 base	
Power Dissipation In W	70 W	
[Us] Rated Supply Voltage	24 V AC/DC	

Complementary

Material	Glass reinforced polyamide 6: base unit Polycarbonate: domed lens unit	
Clamping Connection Capacity	onnection Capacity <= 1 x 1.5 mm ²	
Cable Entry	1 tapped entry for cable gland (included) for M20	
[Ui] Rated Insulation Voltage	250 V conforming to EN/IEC 60947-1	
Current Consumption	< 3100 mA	
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60947-1	
Service Life In Hours	2000 h	
Operating Position	g Position Horizontal	
Flashing Frequency	3 Hz	
Cad Overall Width	rall Width 165 mm	
Cad Overall Height	rall Height 202 mm	
Cad Overall Depth	Depth 165 mm	
Net Weight 1.165 kg		

Environment

Standards	UL 508 CSA C22.2 No 14 EN/IEC 60947-1 EN/IEC 60947-5-1
Protective Treatment	TC
Ambient Air Temperature For Storage	-4070 °C

Ambient Air Temperature For Operation	-2050 °C
Electrical Shock Protection Class	Class I conforming to EN/IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Nema Degree Of Protection	NEMA 4X conforming to UL 508 (indoor) NEMA 4X conforming to CSA C22 (indoor)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Toxic Heavy Metal Free	
⊘	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information