

Product datasheet

Specifications



rotating mirror beacon XVR - Ø 165 - red - 25 W - 230 V AC

XVR1M04

⚠ Discontinued on: Aug 27, 2020

⚠ Discontinued

Main

Range Of Product	Harmony XVR Application
Product Or Component Type	Rotating mirror beacon
Component Name	XVR
Mounting Diameter	165 mm
Light Source	Bulb included, red
Bulb Type	Incandescent with BA 15d base
Power Dissipation In W	25 W
[Us] Rated Supply Voltage	230 V AC

Complementary

Material	Glass reinforced polyamide 6: base unit Polycarbonate: domed lens unit
Clamping Connection Capacity	<= 1 x 1.5 mm²
Cable Entry	1 tapped entry for cable gland (included) for M20
[Ui] Rated Insulation Voltage	250 V conforming to EN/IEC 60947-1
Current Consumption	< 110 mA
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60947-1
Service Life In Hours	2000 h
Operating Position	Horizontal
Flashing Frequency	3 Hz
Cad Overall Width	165 mm
Cad Overall Height	202 mm
Cad Overall Depth	165 mm
Net Weight	1.235 kg

Environment

Standards	CSA C22.2 No 14 EN/IEC 60947-5-1 UL 508 EN/IEC 60947-1
Protective Treatment	TC
Ambient Air Temperature For Storage	-40...70 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-20...50 °C
Electrical Shock Protection Class	Class I conforming to EN/IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Nema Degree Of Protection	NEMA 4X conforming to UL 508 (indoor) NEMA 4X conforming to CSA C22 (indoor)

Contractual warranty

Warranty	18 months
----------	-----------