


Lembar data produk

Spesifikasi



auxiliary contact - 4 OC

48468

Main

Product Or Component Type	Auxiliary contact
Device Short Name	4 OF
Range Compatibility	Masterpact MasterPact NW
Signal Contacts Composition	4 NO/NC

Complementary

Auxiliary Contacts Type	Standard Low level
Mounting Mode	Drawout
Breaking Capacity (A)	AC-12: 10 A at 240/380 V AC 50/60 Hz conforming to EN/IEC 60947-2 AC-12: 10 A at 480 V AC 50/60 Hz conforming to EN/IEC 60947-2 AC-12: 6 A at 690 V AC 50/60 Hz conforming to EN/IEC 60947-2 DC-12: 10 A at 24/48 V DC conforming to EN/IEC 60947-2 DC-12: 10 A at 125 V DC conforming to EN/IEC 60947-2 DC-12: 3 A at 250 V DC conforming to EN/IEC 60947-2 8 A at 480 V AC 50/60 Hz conforming to UL 489 6 A at 600 V AC 50/60 Hz conforming to UL 489 6 A at 250 V DC conforming to UL 489
Minimum Load	100 mA at 24 V 2 mA at 15 V

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	13.0 cm
Package 1 Length	16.0 cm
Package 1 Weight	187.0 g

Contractual warranty

Warranty	12 months
----------	-----------

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

Kinerja kesejahteraan



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information