

Lembar data produk

Spesifikasi



Acti 9 - Auxiliary contact iOF - 1 C/O - AC/DC

A9A26924

⚠ Akan dihentikan pada: 1 Jun 2024

⚠ Dihentikan

Main

Range Of Product	Acti9
Product Or Component Type	OC contact
Device Short Name	iOF
Signal Contacts Composition	1 C/O
[In] Rated Current	AC-12 6 A at 240 V, AC 50/60 Hz AC-12 3 A at 415 V, AC 50/60 Hz DC-12 2 A at 48 V, DC DC-12 1.5 A at 60 V, DC DC-12 1 A at 130 V, DC DC-12 6 A at 24 V, DC
9 Mm Pitches	1

Complementary

[Ui] Rated Insulation Voltage	500 V
[Uimp] Rated Impulse Withstand Voltage	4 kV
Mounting Mode	Clip-on
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	Top: YES
Height	86 mm
Width	9 mm
Depth	73 mm
Net Weight	32 g
Colour	White
Connections - Terminals	Screw clamp terminal (bottom) 1 cable(s) 1...4 mm ² - rigid Screw clamp terminal (bottom) 1 cable(s) 0.5...2.5 mm ² - flexible Screw clamp terminal (bottom) 2 cable(s) 2.5 mm ² - rigid Screw clamp terminal (bottom) 2 cable(s) 1.5 mm ² - flexible with ferrule
Wire Stripping Length	10 mm
Tightening Torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1
Ip Degree Of Protection	IP20 conforming to EN/IEC 60947-5-1
Pollution Degree	3 conforming to EN/IEC 60947-5-1

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Tropicalisation	2 conforming to EN/IEC 60947-5-1
Ambient Air Temperature For Operation	-35...70 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.800 cm
Package 1 Width	2.000 cm
Package 1 Length	9.200 cm
Package 1 Weight	40.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.500 cm
Package 2 Width	10.000 cm
Package 2 Length	27.200 cm
Package 2 Weight	570.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	6.350 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓ Reach Free Of Svhc	
✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information