

Lembar data produk

Spesifikasi



iACTs auxiliary contact 2 NO

A9C15916

Main

Range Of Product	ICT
Range	Acti9
Device Short Name	iACTs
Product Or Component Type	Remote indication auxiliary
Signal Contacts Composition	2 NO

Complementary

Signalling Circuit Voltage	24 V AC/DC: 10 mA 230 V AC: 50/60 Hz 5 A 230 V AC: 50/60 Hz 2 A 130 V DC: 1 A
[Uc] Control Circuit Voltage	24...240 V AC 50/60 Hz 24...130 V DC
Range Compatibility	Acti 9 Acti9 iCT
[Ui] Rated Insulation Voltage	440 V
[Uimp] Rated Impulse Withstand Voltage	4 kV
Mounting Mode	Fixed, on the right of CT
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	1
Height	81 mm
Width	9 mm
Depth	68 mm
Colour	White
Auxiliary Connection Terminal	Tunnel type terminals2 cable(s) flexible 2.5 mm² Tunnel type terminals2 cable(s) rigid 1.5 mm² Tunnel type terminals1 cable(s) rigid 1.5...2.5 mm² Tunnel type terminals1 cable(s) flexible 1.5...2.5 mm²
Wire Stripping Length	9 mm
Tightening Torque	0.8 N.m
Product Compatibility	ICT
Market Segment	Residential Small commercial
Compatibility Code	iACTs

Environment

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Standards	EN 60947-5
Ip Degree Of Protection	IP20 IP20 conforming to IEC 60529
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-20...50 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.7 cm
Package 1 Width	2.1 cm
Package 1 Length	8.8 cm
Package 1 Weight	43.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	8.0 cm
Package 2 Width	9.5 cm
Package 2 Length	23.0 cm
Package 2 Weight	502.0 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	120
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	6.366 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

Kinerja kesejahteraan

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
	Halogen Free Product	
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	