

Lembar data produk

Spesifikasi



linear switch - iSSW - 2 C/O - 20A -
250 V AC - 3 positions

A9E18074

Main

Range Of Product	Acti9
Product Name	Acti9 iSSW
Product Or Component Type	Changeover switch
Device Short Name	iSSW
Device Application	Electrical circuit control
Poles Description	2P
Contacts Type And Composition	2 C/O
[Ue] Rated Operational Voltage	250 V AC 50/60 Hz
Standards	IEC 60947-5-1 IEC 60669-1

Complementary

[Ie] Rated Operational Current	20 A
Control Type	Toggle 3 positions
Marking	1 - 0 - 2
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	4
Height	82 mm
Width	36 mm
Depth	75 mm
Colour	White
Electrical Durability	AC-22: 30000 cycles cos Phi = 0.8
Connections - Terminals	Staggered tunnel terminal (downside) 2 cable(s) 0.5...2.5 mm² flexible Staggered tunnel terminal (downside) 2 cable(s) 0.5...2.5 mm² rigid without cable end
Wire Stripping Length	9 mm
Tightening Torque	1 N.m

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Tropicalisation	2
Pollution Degree	3

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-20...50 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	7.500 cm
Package 1 Length	9.000 cm
Package 1 Weight	88.500 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	8.000 cm
Package 2 Width	10.000 cm
Package 2 Length	23.000 cm
Package 2 Weight	583.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	54
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	5.673 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

Kinerja kesejahteraan

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins