

Lembar data produk

Spesifikasi



miniature circuit breaker - iK60N - 2P - 40 A - C curve

A9K24240

Main

Device Application	Distribution
Range	Acti9
Product Name	Acti9 iK60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	iK60N
Poles Description	2P
Number Of Protected Poles	2
[In] Rated Current	40 A at 30 °C
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Breaking Capacity	6000 A Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1
Suitability For Isolation	Yes conforming to EN/IEC 60898-1
Standards	EN/IEC 60898-1
Product Certifications	SNI

Complementary

Network Frequency	50/60 Hz
Magnetic Tripping Limit	5...10 x In
[Ics] Rated Service Breaking Capacity	6000 A 100 % conforming to EN/IEC 60898-1 - 230 V AC 50/60 Hz
Limitation Class	3 conforming to EN/IEC 60898-1
[Ui] Rated Insulation Voltage	440 V AC 50/60 Hz conforming to EN/IEC 60898-1
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60898-1
Contact Position Indicator	No
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	4
Height	85 mm
Width	36 mm

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Depth	78.5 mm
Net Weight	200 g
Colour	White
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Locking Options Description	Padlocking device
Connections - Terminals	Tunnel type terminal (top or bottom) 1...35 mm² rigid Tunnel type terminal (top or bottom) 1...25 mm² flexible
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	3.5 N.m top or bottom
Earth-Leakage Protection	Without

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Pollution Degree	2 conforming to EN/IEC 60898-1
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	7.5 cm
Package 1 Length	9.4 cm
Package 1 Weight	237 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	8.6 cm
Package 2 Width	9.6 cm
Package 2 Length	21.8 cm
Package 2 Weight	1.49 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	66
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	17.816 kg

Contractual warranty

Warranty	18 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Mercury Free

 Rohs Exemption Information [Yes](#)

 Halogen Free Product

Sertifikasi & Standar

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile No need of specific recycling operations