

Lembar data produk

Spesifikasi



miniature circuit breaker - iK60N - 2P - 6A - C curve

A9K27206

Main

Device Application	Distribution
Range	Acti9
Product Name	Acti9 iK60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	iK60N
Poles Description	2P
Number Of Protected Poles	2
[In] Rated Current	6 A at 30 °C
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Breaking Capacity	6000 A Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1
Suitability For Isolation	Yes conforming to EN/IEC 60898-1
Standards	EN/IEC 60898-1
Product Certifications	SNI

Complementary

Network Frequency	50/60 Hz
Magnetic Tripping Limit	5...10 x In
[Ics] Rated Service Breaking Capacity	6000 A 100 % conforming to EN/IEC 60898-1 - 230 V AC 50/60 Hz
Limitation Class	3 conforming to EN/IEC 60898-1
[Ui] Rated Insulation Voltage	440 V AC 50/60 Hz conforming to EN/IEC 60898-1
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60898-1
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	4
Height	85 mm
Width	36 mm
Depth	78.5 mm

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Net Weight	200 g
Colour	White
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Locking Options Description	Padlocking device
Connections - Terminals	Tunnel type terminal (top or bottom) 1...25 mm² rigid Tunnel type terminal (top or bottom) 1...16 mm² flexible
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	2 N.m top or bottom
Earth-Leakage Protection	Without

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Pollution Degree	2 conforming to EN/IEC 60898-1
Overvoltage Category	III
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	9.5 cm
Package 1 Length	3.4 cm
Package 1 Weight	196 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	6
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	1215 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	66
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	14208 g

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations