

Lembar data produk

Spesifikasi



cartridge C65-350 for surge arrester iPRD

A9L65102

Main

Product Or Component Type	Cartridge
Device Short Name	C65-350
Surge Arrester Type	Electrical distribution network

Complementary

Surge Arrester Class Type	Type 2
Surge Arrester Technology	MOV
Product Destination	Surge protection device iPRD65r 1P Surge protection device iPRD65r 2P Surge protection device iPRD65r 3P Surge protection device iPRD65r 4P
Earthing System	TN TT
[Ue] Rated Operational Voltage	230 V AC 50 Hz
Nominal Discharge Current	20 kA
Maximum Discharge Current	65 kA
[Uc] Maximum Continuous Operating Voltage	350 V
Maximum [Up] Voltage Protection Level	<1.5 kV type 2
Local Signalling	Flag (white/red)
Mounting Mode	Plug-in
Mounting Support	Into SPD module
9 Mm Pitches	2
Height	57 mm
Width	18 mm
Depth	56 mm
Net Weight	0.075 kg
Colour	White (RAL 9003)
Material	PBT (polybutylene terephthalate)
Response Time	< 25 ns

Environment

Standards	EN 61643-11 IEC 61643-11: 2011
Quality Labels	CE

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Ip Degree Of Protection	IP20 front face:
Relative Humidity	5...90 %
Operating Altitude	0...2000 m
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	7.5 cm
Package 1 Length	9 cm
Package 1 Weight	100 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8 cm
Package 2 Width	10 cm
Package 2 Length	28.5 cm
Package 2 Weight	1.293 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	12.35 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Reach Free Of Svhc

 Rohs Exemption Information [Yes](#)

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information