

# Lembar data produk

Spesifikasi



## Acti 9 - comb busbar - 3L - 18 mm pitch - 24 modules - 100A



A9XPH324

### Main

|                                    |                      |
|------------------------------------|----------------------|
| Range                              | Acti9                |
| Product Or Component Type          | Comb busbar          |
| Mounting Mode                      | Horizontal           |
| Accessory / Separate Part Category | Connection accessory |
| Lines Description                  | 3L                   |
| Length In 18 Mm Modules            | 24                   |

### Complementary

|                                |                                                                                                                                                  |
|--------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| Number Of Ways                 | 8 ways 3 L                                                                                                                                       |
| Poles Configuration For 1 Way  | 1 x 3P                                                                                                                                           |
| Connection Pitch               | 18 mm                                                                                                                                            |
| Connector Type                 | Tooth                                                                                                                                            |
| Distance Between Way           | 54 mm                                                                                                                                            |
| Marking                        | L1 L2 L3                                                                                                                                         |
| Insulation                     | Insulated                                                                                                                                        |
| Device Presentation            | Cuttable                                                                                                                                         |
| [Ie] Rated Operational Current | 100 A at 40 °C                                                                                                                                   |
| [Ue] Rated Operational Voltage | 415 V AC                                                                                                                                         |
| [Ui] Rated Insulation Voltage  | 500 V AC conforming to IEC 61439-2                                                                                                               |
| Mounting Location              | Top or bottom on tunnel type terminals<br>Top or bottom on double terminal                                                                       |
| 9 Mm Pitches                   | 48                                                                                                                                               |
| Width                          | 430 mm                                                                                                                                           |
| Colour                         | White (RAL 9003)                                                                                                                                 |
| Range Compatibility            | Acti 9 Acti9 iC60<br>Acti 9 Acti9 iK60<br>Acti 9 Acti9 iLD<br>Acti 9 Acti9 iLD K<br>Acti 9 Acti9 iSW<br>Acti 9 Acti9 iSW-NA<br>Multi9 Multi9 C60 |

### Environment

|           |                              |
|-----------|------------------------------|
| Standards | IEC 60947-7-1<br>IEC 61439-2 |
|-----------|------------------------------|

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

|                         |                                             |
|-------------------------|---------------------------------------------|
| Fire Resistance         | 960 °C ( 30 s ) conforming to IEC 60695-2-1 |
| Pollution Degree        | 3 conforming to IEC 60947-7-1               |
| Ip Degree Of Protection | IP20 with end-pieces and tooth covers       |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 3 cm     |
| Package 1 Width              | 1.5 cm   |
| Package 1 Length             | 43 cm    |
| Package 1 Weight             | 232 g    |
| Unit Type Of Package 2       | BB1      |
| Number Of Units In Package 2 | 5        |
| Package 2 Height             | 6 cm     |
| Package 2 Width              | 8.7 cm   |
| Package 2 Length             | 46.6 cm  |
| Package 2 Weight             | 1.278 kg |
| Unit Type Of Package 3       | S04      |
| Number Of Units In Package 3 | 40       |
| Package 3 Height             | 30 cm    |
| Package 3 Width              | 40 cm    |
| Package 3 Length             | 60 cm    |
| Package 3 Weight             | 11 kg    |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 12 months |
|----------|-----------|

Keberlanjutan



**Green Premium™** label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO<sub>2</sub>.

**Panduan untuk menilai keberlanjutan produk** adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi   RoHS/REACH

## Kinerja kesejahteraan

|   |                            |     |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc         |     |
| ✓ | Toxic Heavy Metal Free     |     |
| ✓ | Mercury Free               |     |
| ✓ | Rohs Exemption Information | Yes |

## Sertifikasi & Standar

|                          |                                                                                                                             |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Reach Regulation         | <a href="#">REACH Declaration</a>                                                                                           |
| Eu Rohs Directive        | Compliant<br><a href="#">EU RoHS Declaration</a>                                                                            |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope)                 |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>                                                                               |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | No need of specific recycling operations                                                                                    |