

# Lembar data produk

Spesifikasi



Cable end, Linergy TR cable ends, twin conductor, grey, 0.75mm<sup>2</sup>, for insulated cable, medium size, 5 sets of 50

AZ5DE007D

## Main

|                           |                      |
|---------------------------|----------------------|
| Range Of Product          | Linergy              |
| Product Or Component Type | Cable end            |
| Cable End Size            | Medium               |
| Standards                 | DIN 46228-4          |
| Type Of Packing           | Dispenser pack       |
| Quantity Per Set          | 5 sets of 100        |
| Cable Cross Section       | 0.75 mm <sup>2</sup> |

## Complementary

|                        |                               |
|------------------------|-------------------------------|
| Cable End Type         | Twin conductor                |
| Additional Information | Without marker tag holder     |
| Colour                 | Blue                          |
| Bezel Material         | Halogen-free plastic          |
| Tube Material          | Copper conforming to ISO 1337 |
| Number Of Cables       | 2                             |
| Awg Gauge              | AWG 20                        |
| Bezel Size             | Ø 2.8 x 5 mm                  |
| Tube Diameter          | 2 mm                          |
| Length                 | 15 mm                         |
| Tube Length            | 8 mm                          |
| Net Weight             | 0.13 kg                       |

## Environment

|                                       |              |
|---------------------------------------|--------------|
| Product Certifications                | cCSAus       |
| Ambient Air Temperature For Operation | -20...105 °C |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 0.400 cm |
| Package 1 Width              | 0.400 cm |
| Package 1 Length             | 1.400 cm |

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

|                              |           |
|------------------------------|-----------|
| Package 1 Weight             | 0.100 g   |
| Unit Type Of Package 2       | BB1       |
| Number Of Units In Package 2 | 500       |
| Package 2 Height             | 13.000 cm |
| Package 2 Width              | 7.000 cm  |
| Package 2 Length             | 12.600 cm |
| Package 2 Weight             | 126.000 g |
| Unit Type Of Package 3       | S02       |
| Number Of Units In Package 3 | 5000      |
| Package 3 Height             | 15.000 cm |
| Package 3 Width              | 30.000 cm |
| Package 3 Length             | 40.000 cm |
| Package 3 Weight             | 1.605 kg  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Keberlanjutan



**Green Premium™** label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO<sub>2</sub>.

**Panduan untuk menilai keberlanjutan produk** adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



RoHS/REACH

Kinerja kesejahteraan

|   |                                    |     |
|---|------------------------------------|-----|
| ✓ | Reach Free Of Svhc                 |     |
| ✓ | Toxic Heavy Metal Free             |     |
| ✓ | Mercury Free                       |     |
| ✓ | Rohs Exemption Information         | Yes |
| ✓ | Pvc Free                           |     |
| ✓ | Halogen Free Plastic Parts Product |     |

Sertifikasi & Standar

|                       |                                                                                                             |
|-----------------------|-------------------------------------------------------------------------------------------------------------|
| Reach Regulation      | <a href="#">REACH Declaration</a>                                                                           |
| Eu Rohs Directive     | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Circularity Profile   | No need of specific recycling operations                                                                    |