

Lembar data produk

Spesifikasi



AD63 K - earth leakage circuit breaker - 1P+N - C - 25A - 30mA - 4500A - AC-TYPE

DOM12524

⚠ Telah dihentikan pada: 7 Des 2021

⚠ Dihentikan

Main

Range	Domae
Device Application	Distribution
Product Name	AD63 K
Product Or Component Type	Residual current breaker with overcurrent protection (RCBO)
Poles Description	1P + N
Neutral Position	Left
Earth-Leakage Protection Class	Type AC
Suitability For Isolation	Yes

Complementary

[In] Rated Current	25 A at 30 °C
Network Type	AC
Network Frequency	50 Hz
[Ue] Rated Operational Voltage	230/240 V AC 50 Hz
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Magnetic Tripping Limit	5...10 x In
Earth-Leakage Sensitivity	30 mA
Earth-Leakage Protection Time Delay	Instantaneous
Breaking Capacity	4500 A Icn at 230/240 V AC 50 Hz
Electrical Insulation Class	Class II
Limitation Class	3
[Ui] Rated Insulation Voltage	400 V AC 50 Hz
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	YES
9 Mm Pitches	2
Height	93 mm

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Width	18 mm
Depth	70 mm
Net Weight	136 g
Colour	Grey
Mechanical Durability	20000 cycles
Provision For Padlocking	Padlockable
Locking Options Description	By padlocks
Connections - Terminals	Screw clamp terminal (upstream) 1...16 mm² rigid Screw clamp terminal (upstream) 1...16 mm² flexible Screw clamp terminal (downstream) 1...10 mm² rigid Screw clamp terminal (downstream) 1...10 mm² flexible
Wire Stripping Length	14 mm for upstream connection 11 mm for downstream connection
Tightening Torque	2 N.m upstream 2 N.m downstream
Earth-Leakage Protection	Integrated

Environment

Standards	IEC 61009-2-2 IEC 61009-1
Product Certifications	SNI
Ambient Air Temperature For Operation	-25...55 °C
Ambient Air Temperature For Storage	-30...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	7.2 cm
Package 1 Length	9.25 cm
Package 1 Weight	141 g

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Mercury Free

 Rohs Exemption Information [Yes](#)

Sertifikasi & Standar

Eu Rohs Directive [Compliant](#)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)