

Lembar data produk

Spesifikasi



Miniature circuit breaker, Domae, 2P, 16 A, C Curve, 6000 A

DOMF01216

Main

Range	Domae
Product Or Component Type	Miniature circuit-breaker
Device Short Name	Domae MCB
Device Application	Protection
Poles Description	2P
Number Of Protected Poles	1
Neutral Position	Left
[In] Rated Current	16 A
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Breaking Capacity	Icn 6000 A
Quality Labels	CE

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Magnetic Tripping Limit	5...10 x In
Control Type	Toggle
Mounting Mode	Clip-on
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	YES
Connection Pitch	18 mm between phases
9 Mm Pitches	4
Height	81 mm
Width	36 mm
Depth	71.5 mm
Net Weight	0.190 kg
Colour	White
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Connections - Terminals	Tunnel type terminals (top or bottom) - 1...25 mm² - rigid Tunnel type terminals (top or bottom) - 1...16 mm² - flexible
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	2 N.m top or bottom
Earth-Leakage Protection	Without

Environment

Standards	IEC 60898-1
Product Certifications	SNI
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Overvoltage Category	III
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-5...60 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	1.8 cm
Package 1 Length	8.5 cm
Package 1 Weight	194 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	6
Package 2 Height	8 cm
Package 2 Width	8.5 cm
Package 2 Length	22.5 cm
Package 2 Weight	1.413 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	72
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	17.67 kg

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations