

Lembar data produk

Spesifikasi



S-Classic - bell press switch - 1 gang - white, blister

E31_1RBPRPA_WE_G12

⚠ Telah dihentikan pada: 14 Apr 2023

⚠ Dihentikan

Main

Range	S-Classic
Product Or Component Type	Bell press switch
Device Application	Control
Switch Application	Bell switch
Quantity Per Set	Set of 1

Complementary

Control Type	Push-button
Actuator	Push-button
Number Of Gangs	1 gang
Device Mounting	Surface Flush
Rated Current	10 AX at 250 V AC
Material	Plate: PC (polycarbonate), white Dolly: PC (polycarbonate), white Base: PA66, black
Embedding Depth	12.3 mm
Height	87 mm
Width	87 mm
Depth	28.9 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	IEC 60669-1 MS IEC 60669-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.6 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Package 1 Weight	55 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9 cm
Package 2 Width	14.8 cm
Package 2 Length	18 cm
Package 2 Weight	449.08 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	20.3 cm
Package 3 Width	30.5 cm
Package 3 Length	40.9 cm
Package 3 Weight	5500 g