

Lembar data produk

Spesifikasi



current transformer tropicalised
DIN mount 250 5 cables d. 27 -
bars 10x32 15x25

METSECT5MA025

Main

Range	PowerLogic
Product Name	CT
Product Or Component Type	Current transformer
Secondary Current	5 A
Accuracy Class	Class 0.5 at 6 VA Class 1 at 8 VA
[In] Rated Current	250 A

Complementary

Current Transformer Type	Tropicalised for busbar and cable
Current Transformer Ratio	250/5
[Ith] Conventional Free Air Thermal Current	15 kA
Dynamic Withstand Current	2.5 Ith
Maximum Safety Factor	5
[Ue] Rated Operational Voltage	< 720 V AC 50/60 Hz
[Ui] Rated Insulation Voltage	3 kV
Mounting Mode	Clip-on Insulated locking screw By screws
Mounting Support	DIN rail Busbar Mounting plate
Width	Outside: 56 mm
Height	Outside: 80 mm
Depth	Frame : 43 mm Total : 63 mm
Diameter	27 mm
Net Weight	0.298 kg
[Uimp] Rated Impulse Withstand Voltage	3 kV
Electrical Insulation Class	Class B
Cable Outer Diameter	27 mm
Opening Of Bars	25.5 x 15.5 32.5 x 10.5
Sealing	Without

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Environment

Standards	IEC 61869-2 VDE 0414
Product Certifications	EAC CE
Ip Degree Of Protection	IP20
Relative Humidity	0...95 %
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	7 cm
Package 1 Length	9 cm
Package 1 Weight	304 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	35
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	11.08 kg

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



RoHS/REACH

Kinerja kesejahteraan



Mercury Free



Rohs Exemption Information

Yes

Sertifikasi & Standar

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)

Weeee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins