

Lembar data produk

Spesifikasi



mini Pragma surface enclosure - 1 x 4 modules - plain door

MIP12104

Main

Range	Resi9
Product Name	Resi9 MP
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	4
Nb Of Horizontal Rows	1
Type Of Door	Plain
Width	Outside: 124 mm
Height	Outside: 198 mm
Depth	Outside : 95 mm

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	8
Total Number Of 18 Mm Modules	4
[In] Rated Current	50 A
Type Of Rail	35 mm asymmetrical rail
Mounting Plate Description	Without mounting plate
Cable Entry	1 bare flange 1 trunking flange
Terminal Block Function	Earth / neutral
Number Of Terminal Blocks	1 earth (screwed) with 4 outgoing 1 neutral (screwed) with 4 outgoing
Distribution Block Outgoers	1 x 16 mm ² for earth 1 x 16 mm ² for neutral 1 x 6 mm ² for earth 1 x 6 mm ² for neutral 2 x 10 mm ² for earth 2 x 10 mm ² for neutral
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Internal Depth	74 mm
Colour	Door: white (RAL 9003) Front face: white (RAL 9003)
Market Segment	Small commercial Residential

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Environment

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality Labels	IMQ
Fire Resistance	Door: 650 °C Back part: 650 °C Front face: 650 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.55 cm
Package 1 Width	12.4 cm
Package 1 Length	19.8 cm
Package 1 Weight	400 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	20
Package 2 Height	52 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	8.1 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	160
Package 3 Height	60 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	76.8 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations