

Lembar data produk

Spesifikasi



Climasys CC - Electronical thermostat 200..240V - range of temperature -40...80°C

NSYCCOTH230VID

Main

Range	ClimaSys
Product Name	ClimaSys CC
Product Or Component Type	Electronical thermostat
Temperature Setting Range	-40...80 °C
Display Type	OLED screen
Information Displayed	Temperature in °F Temperature in °C

Complementary

Input Voltage	200...240 V AC
Sensor Type	Optional NTC external sensor
Maximum Switching Capacity	4 A 230 V AC
Electrical Connection	10 terminals, clamping capacity: 2.5 mm²
Mounting Mode	Clipped By screws
Height	85 mm external:
Width	56 mm external:
Depth	44 mm external:
Mounting Location	Cross rails On mounting plate Spacial upright 35 mm DIN rail
Ambient Air Temperature For Operation	-40...80 °C
Hysteresis	2 K programmed value
Number Of Outputs	2 ventilation/heating function
Material	PC
Colour	Light grey
Flame Retardance	Self-extinguishing conforming to UL94 (material V0)
Product Certifications	UR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Package 1 Width	7.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	140 g
Unit Type Of Package 2	PAL
Number Of Units In Package 2	75
Package 2 Height	46 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	11.625 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Mercury Free

 Rohs Exemption Information [Yes](#)

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations