

Lembar data produk

Spesifikasi



ClimaSys CC - simple thermostat
250V - range of temperature 0...
60°C - NC - °C

NSYCCOTHC

Main

Range	ClimaSys
Product Name	ClimaSys CC
Product Or Component Type	Simple thermostat
Temperature Setting Range	0...60 °C
Information Displayed	Temperature in °C

Complementary

Input Voltage	250 V
Sensor Type	Bimetal
Contacts Type And Composition	NC
Contact Resistance	10 mOhm
Service Life In Cycles	100000 cycles
Maximum Switching Capacity	2 A 120...250 V AC inductive pf: 0.6 10 A 250 V AC resistive 15 A 120 V AC resistive 30 W DC
Electrical Connection	4 terminals, clamping capacity: 2.5 mm²
Mounting Mode	Clipped
Height	68 mm external:
Width	33 mm external:
Depth	44 mm external:
Net Weight	40 g
Mounting Location	Spacial upright 35 mm DIN rail Cross rails On mounting plate
Ambient Air Temperature For Operation	-20...80 °C
Ip Degree Of Protection	IP20
Hysteresis	7 K +/- 0.4K
Number Of Outputs	1 heating function
Material	PC
Colour	Light grey
Flame Retardance	Self-extinguishing conforming to UL94 (material V0)
Product Certifications	UL

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.826 cm
Package 1 Width	6.35 cm
Package 1 Length	8.128 cm
Package 1 Weight	63.504 g
Unit Type Of Package 2	PAM
Number Of Units In Package 2	3600
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	160 cm
Package 2 Weight	290 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Mercury Free

 Rohs Exemption Information [Yes](#)

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations