

# Lembar data produk

Spesifikasi



Spacial CRN plain door w/o  
mount.plate. H600xW400xD200  
IP66 IK10 RAL7035..

NSYCRN64200

## Main

|                             |                                                   |
|-----------------------------|---------------------------------------------------|
| Range                       | Spacial                                           |
| Product Name                | Spacial CRN                                       |
| Application                 | Multi-purpose                                     |
| Category                    | Compact enclosure                                 |
| Enclosure Nominal Height    | 600 mm                                            |
| Enclosure Nominal Width     | 400 mm                                            |
| Enclosure Nominal Depth     | 200 mm                                            |
| Installation Accessory Type | Wall-mounting                                     |
| Device Composition          | 1 body<br>1 cable gland plate<br>1 door<br>1 lock |
| Door Type                   | Plain                                             |
| Mounting Plate Description  | Without mounting plate                            |

## Complementary

|                             |                                                                                                            |
|-----------------------------|------------------------------------------------------------------------------------------------------------|
| Body Type                   | Sides made from a single folded section<br>Back welded with double profile forming a protected sealed area |
| Number Of Doors             | Front face: 1 door(s)                                                                                      |
| Door Opening Side           | Reversible (120 °)                                                                                         |
| Lock Type                   | 3 mm double-bar lock                                                                                       |
| Type Of Gland Plate         | Standard                                                                                                   |
| Accessibility For Operation | Front                                                                                                      |
| Removable Parts             | Door by hinges<br>Cable gland plate by screws                                                              |
| Material                    | Body: steel                                                                                                |
| Surface Finish              | Epoxy-polyester powder                                                                                     |
| Colour                      | Grey (RAL 7035)                                                                                            |
| Standards                   | IEC 62208                                                                                                  |
| Product Certifications      | cUL<br>UL<br>DNV-GL                                                                                        |
| Net Weight                  | 9.83 kg                                                                                                    |

## Environment

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

|                         |                              |
|-------------------------|------------------------------|
| Ip Degree Of Protection | IP66 conforming to IEC 60529 |
| Ik Degree Of Protection | IK10 conforming to IEC 62262 |

## Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type Of Package 1       | PCE        |
| Number Of Units In Package 1 | 1          |
| Package 1 Height             | 22.000 cm  |
| Package 1 Width              | 41.000 cm  |
| Package 1 Length             | 61.500 cm  |
| Package 1 Weight             | 9.800 kg   |
| Unit Type Of Package 2       | PAM        |
| Number Of Units In Package 2 | 30         |
| Package 2 Height             | 220.000 cm |
| Package 2 Width              | 100.000 cm |
| Package 2 Length             | 120.000 cm |
| Package 2 Weight             | 307.000 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 12 months |
|----------|-----------|

Keberlanjutan



**Green Premium™** label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO<sub>2</sub>.

**Panduan untuk menilai keberlanjutan produk** adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi   RoHS/REACH

Kinerja kesejahteraan

 Mercury Free

 Rohs Exemption Information   [Yes](#)

Sertifikasi & Standar

|                          |                                                                                                                       |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Reach Regulation         | <a href="#">REACH Declaration</a>                                                                                     |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)                                                            |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>                                                                         |
| Circularity Profile      | No need of specific recycling operations                                                                              |