

Lembar data produk

Spesifikasi



NSYTR partition plate for screw single-level terminal block 1x1 - 2.5 to 10mm²

NSYTRAP22

Main

Range	Lineryg
Product Name	Lineryg TR
Product Or Component Type	Partition
Device Short Name	TRA
Accessory / Separate Part Category	Insulation accessory
Product Compatibility	TRV screw terminal - passthrough terminal block, length = 47.7 mm TRV screw terminal - protective earth terminal block, length = 47.7 mm TRV screw terminal - blade disconnect terminal block, length = 55 mm
Thickness	2 mm

Complementary

Cable Cross Section	2.5 mm² 6 mm² 10 mm² 4 mm²
Number Of Connections	2
Number Of Measurement Input	2 1
Quantity Per Set	Set of 50
Net Weight	4.9 g
Colour	Grey

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.500 cm
Package 1 Width	5.000 cm
Package 1 Length	5.500 cm
Package 1 Weight	5.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	3.000 cm
Package 2 Width	17.000 cm
Package 2 Length	17.000 cm

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Package 2 Weight	250.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	1600
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	8.550 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

Kinerja kesejahteraan

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
	Halogen Free Plastic Parts Product	

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)