

Lembar data produk

Spesifikasi



Flatbed plotter, Linergy TR, ready to use, A4 format, External supply 100 to 240VAC 50/60Hz, Internal supply 24VDC

NSYTRAPLOT

Main

Range	Linergy
Product Name	TR
Product Or Component Type	Flatbed plotter
Device Short Name	TRA
Accessory / Separate Part Category	Marking accessory

Complementary

Product Compatibility	Legend ZBY HP plotter pen Marking card TRA
[Ue] Rated Operational Voltage	External supply: 100...240 V AC 50/60 Hz Internal supply: 24 V DC
[Ie] Rated Operational Current	external supply: AC 50/60 Hz internal supply: DC
Material	Aluminium
Provided Equipment	Installation guide Power supply USB cable Documentation
Integrated Connection Type	USB port
Label Dimensions	220 x 305 mm
Passing Speed Of Object	40 mm/s
Buffer Size	16 MB
Motor Type	2-phase stepper motor
Repeat Accuracy	+/- 0.05 mm
Height	125 mm
Width	440 mm
Length	440 mm
Net Weight	6 kg
Colour	Grey

Environment

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Standards	EN 61000-4-6
	EN 55022 class B
	EN 61000-4-5
	EN 61000-4-2
	EN 61000-4-4
	EN 60950-1
	EN 61000-4-3
	EN 61000-4-11
Ambient Air Temperature For Operation	10...35 °C
Ambient Air Temperature For Storage	-10...50 °C
Relative Humidity	35...75 % in operation
	10...90 % in storage

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	23.0 cm
Package 1 Width	56.0 cm
Package 1 Length	56.0 cm
Package 1 Weight	9.5 kg

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



RoHS/REACH

Kinerja kesejahteraan

✓

Mercury Free

✓

Rohs Exemption Information

Yes

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Circularity Profile	No need of specific recycling operations