

# Lembar data produk

Spesifikasi



## SWITCHING JUMPER, 3PTS, FOR NSYTRV62TTD TERMINAL, ORANGE

NSYTRASJ3

⚠ Telah dihentikan pada: 30 Sep 2021

⚠ Dihentikan

### Main

|                                    |                                                                                                                                               |
|------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Range                              | Linergy                                                                                                                                       |
| Product Name                       | Linergy TR                                                                                                                                    |
| Product Or Component Type          | Switching jumper                                                                                                                              |
| Device Short Name                  | TRA                                                                                                                                           |
| Accessory / Separate Part Category | Measurement accessory                                                                                                                         |
| Product Compatibility              | TRV screw terminal - passthrough terminal block, length = 100.8 mm<br>TRV screw terminal - blade disconnect terminal block, length = 100.8 mm |

### Complementary

|                             |                   |
|-----------------------------|-------------------|
| Cable Cross Section         | 6 mm <sup>2</sup> |
| Number Of Connections       | 2                 |
| Number Of Measurement Input | 6                 |
| Quantity Per Set            | Set of 10         |
| Net Weight                  | 15.5 g            |
| Colour                      | Orange            |

### Packing Units

|                              |       |
|------------------------------|-------|
| Unit Type Of Package 1       | PCE   |
| Number Of Units In Package 1 | 1     |
| Package 1 Height             | 5 cm  |
| Package 1 Width              | 15 cm |
| Package 1 Length             | 17 cm |
| Package 1 Weight             | 16 g  |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Keberlanjutan



**Green Premium™** label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO<sub>2</sub>.

**Panduan untuk menilai keberlanjutan produk** adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



RoHS/REACH

Kinerja kesejahteraan

|                                                              |                |
|--------------------------------------------------------------|----------------|
| <div><div>✓</div><div>Reach Free Of Svhc</div></div>         |                |
| <div><div>✓</div><div>Toxic Heavy Metal Free</div></div>     |                |
| <div><div>✓</div><div>Mercury Free</div></div>               |                |
| <div><div>✓</div><div>Rohs Exemption Information</div></div> | <div>Yes</div> |

Sertifikasi & Standar

|                                  |                                                                                                                                |
|----------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| <div>Eu Rohs Directive</div>     | <div>Pro-active compliance (Product out of EU RoHS legal scope)</div> <div><a href="#">EU RoHS Declaration</a></div>           |
| <div>China Rohs Regulation</div> | <div><a href="#">China RoHS declaration</a></div> <div>Pro-active China RoHS declaration (out of China RoHS legal scope)</div> |