

Lembar data produk

Spesifikasi



Xightor indoor video station - 7 inch touch screen module

VEETS07

⚠ **Telah dihentikan pada:** 14 Apr 2023

⚠ **Dihentikan**

Main

Range	Xightor
Product Or Component Type	Indoor video station
Intercom Type	2-way intercom
Use Of Slot	SD card
Calling Button	1 button
Control Button Type	Reset Door opener button Voice connection button
Display Size	7 inch
Language	English/Chinese
Colour Tint	Black
Supply	External supply
Market Segment	Residential

Complementary

Device Composition	Camera CMOS
Mounting Mode	Flush-mounted
Device Mounting	Flush
Mounting Support	86 x 86 mm mounting box
Safety Function	SOS (safe operating stop) 8 alarm zones
Display Type	LCD touch screen
Display Resolution	800 x 480 pixels
Function Available	Factory reset Touch function Setting mode
Mounting Position	Horizontal
Local Signalling	LED power supply LED ethernet connection LED communication data bus
Information Displayed	Menu-driven user interface
Character Font	ASCII (European characters) Taiwanese (traditional Chinese) Chinese (simplified Chinese)
[Ue] Rated Operational Voltage	12 V DC

Disclaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna.

[In] Rated Current	2 A
Power Consumption In W	3.5 W
Signalling Type	16 adjustable ring tones
[Us] Rated Supply Voltage	12 V DC, 2 A
Output Type	Relay 30 V DC Alarm output
Integrated Connection Type	2 RS485 1 RS232 1 Ethernet port
Maximum Power Consumption In W	3.5 W
Height	150 mm
Width	230 mm
Depth	16 mm
Net Weight	500 g

Environment

Ambient Air Temperature For Operation	-10...60 °C
Relative Humidity	0...90 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	18.8 cm
Package 1 Length	26.5 cm
Package 1 Weight	600.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	29.5 cm
Package 2 Width	39.6 cm
Package 2 Length	54.0 cm
Package 2 Weight	12.01 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	240
Package 3 Height	89.5 cm
Package 3 Width	90.0 cm
Package 3 Length	109.0 cm
Package 3 Weight	144.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

Kinerja kesejahteraan

✓ Reach Free Of Svhc	
✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)