



Price* : 132.550,00 IDR



Main

| | |
|----------------------------|--------------------------------------|
| Range of product | OsiSense XC |
| Series name | Standard format |
| Product or component type | Limit switch lever |
| Device short name | ZCKY |
| Product compatibility | XCKL XCKM XCKS |
| Associated head | ZCKD05 |
| Movement of operating head | Rotary |
| Type of operator | Roller lever spring return metal (-) |
| Type of approach | Lateral approach |

Complementary

| | |
|------------------|------------|
| Switch actuation | By 30° cam |
| Positive opening | With |

Environment

| | |
|---------------------------------------|--------------------------------------|
| Ambient air temperature for operation | -25...70 °C for standard environment |
| Ambient air temperature for storage | -40...70 °C for standard environment |
| Environmental characteristic | Standard environment |

Offer Sustainability

| | |
|--------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1014 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold |

Reference not containing SVHC above the threshold

| | |
|----------------------------------|---------------------------------------|
| Product end of life instructions | Need no specific recycling operations |
|----------------------------------|---------------------------------------|

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
