



Price\* : 34.650,00 IDR



### Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCY
Product compatibility	XCKD XCKP XCKT XCMD
Associated head	ZCE01 ZCE05
Movement of operating head	Rotary
Type of operator	Roller lever spring return thermoplastic
Tracks	16/39 mm for XCMD 21/44 mm for XCKD 21/44 mm for XCKP 21/44 mm for XCKT
Type of approach	Lateral approach

### Complementary

Switch actuation	By 30° cam
Positive opening	With

### Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

### Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 0851 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations <a href="#">End of Life Information</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------