



# MOUNTING PLATE VIGI NSX/ CVS 250 HZ.FIXED TOGGLE

03033

! Discontinued on: 9 Aug 2023



### Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type Mounting plate	
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure
Installation Description	Floor-standing enclosure - width 850 mm Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Installed Device	ComPact: fixed NSX100250 and ammeter without earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS100160 with earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS250 with earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX100160 with earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX250 with earth leakage protection - control: toggle - horizontal installation
Poles Description	1 x 3P: fixed CVS100160 horizontal installation 1 x 4P: fixed CVS100160 horizontal installation 1 x 3P: fixed CVS250 horizontal installation 1 x 4P: fixed CVS250 horizontal installation 1 x 4P: fixed NSX100160 horizontal installation 1 x 4P: fixed NSX100160 horizontal installation 1 x 3P: fixed NSX250 horizontal installation 1 x 4P: fixed NSX250 horizontal installation 1 x 4P: fixed NSX250 horizontal installation 1 x 3P: fixed NSX100250 and ammeter horizontal installation 1 x 4P: fixed NSX100250 and ammeter horizontal installation
Condition Of Using Cable Tie	Need additional plate (2M high) when installation of device is in horizontal

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Number Of Vertical Modules [50 Mm]

- 4 module(s): CVS100...160 with earth leakage protection , direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top or bottom of enclosure)
- 4 module(s): CVS100...160 with earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top or bottom of enclosure)
- 4 module(s): CVS250 with earth leakage protection , direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top or bottom of enclosure)
- 4 module(s): CVS250 with earth leakage protection, direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top or bottom of enclosure)
- 4 module(s): NSX100...160 with earth leakage protection , direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top or bottom of enclosure)
- 4 module(s): NSX100...160 with earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top or bottom of enclosure)
- 4 module(s): NSX100...160 with earth leakage protection , direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)
- 4 module(s): NSX250 with earth leakage protection, direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top or bottom of enclosure)
- 4 module(s): NSX250 with earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top or bottom of enclosure)
- 4 module(s): NSX250 with earth leakage protection , direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)
- 4 module(s): NSX100...250 and ammeter without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top or bottom of enclosure)
- 4 module(s): NSX100...250 and ammeter without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top or bottom of enclosure)
- 4 module(s): CVS100...160 with earth leakage protection , direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)
- 4 module(s): CVS250 with earth leakage protection , direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)

Standards	IEC 61439-2
Product Certifications	ASEFA

### Complementary

Cable Entry	Cut-out plates 0.31 mm top or bottom 42 mm
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)
Width	600 mm
Height	150 mm
Net Weight	0.94 kg

#### Functional Unit

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...250 and ammeter without fixed toggle horizontal 3P 1 direct with long terminal shield 4 0.31 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...250 and ammeter without fixed toggle horizontal 3P 1 direct with long terminal shield 4 0.31 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...250 and ammeter without fixed toggle horizontal 4P 1 direct with long terminal shield 4 0.31 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...250 and ammeter without fixed toggle horizontal 4P 1 direct with long terminal shield 4 0.31 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS100...160 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS100...160 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS100...160 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS100...160 with fixed toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS100...160 with fixed toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS100...160 with fixed toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS250 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS250 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS250 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS250 with fixed toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS250 with fixed toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS250 with fixed toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...160 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...160 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...160 with fixed toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...160 with fixed toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 with fixed toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX250 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX250 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm

850 mm Prisma G floor-standing enclosure ComPact NSX250 with fixed toggle

850 mm Prisma G floor-standing enclosure ComPact NSX250 with fixed toggle

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX250 with fixed

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX250 with fixed

horizontal 3P 1 direct with long terminal shield 4 0.31 mm

horizontal 4P 1 direct with long terminal shield 4 0.31 mm

toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	19.0 cm
Package 1 Length	47.0 cm
Package 1 Weight	940.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	10

Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	10.6 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	120
Package 3 Height	105.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	112.8 kg



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>Ø</b>	Halogen Free Plastic Parts Product

### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile