Product datasheet

Specifications





WALL-MOUNTED ENCLOSURE W600 27M PRISMA G IP55

08307

() Discontinued on: 9 Aug 2023

① Discontinued

Main

| Range | Prisma |
|---------------------------------------|--|
| Range Of Product | Prisma G |
| Product Or Component Type | Enclosure |
| Device Application | Low voltage electrical distribution |
| Enclosure Type | Functional enclosure delivered in kit form |
| Enclosure/Cubicle Description | Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm |
| Enclosure Mounting | Surface |
| Additional Information | Can be combined side by side and one on top of another |
| Type Of Front Plate | Without to be ordered separately |
| Number Of Vertical Modules [50 Mm] | 27 |
| Number Of 18 Mm Modules Per Row | 24 |
| Standards | IEC 61439-1 IEC 61439-2 IEC 62208 |

Complementary

| [Ui] Rated Insulation Voltage | 1000 V on main rear busbars conforming to IEC 61439-2 |
|---|--|
| Network Frequency | 50/60 Hz |
| [In] Rated Current | 630 A at 40 °C conforming to IEC 61439-2 |
| [Icw] Rated Short-Time Withstand Current | 25 kA 1 s conforming to IEC 61439-2 |
| [lpk] Rated Peak Withstand Current | 53 kA conforming to IEC 61439-2 |
| Electrical Insulation Class | Class I |
| Protective Treatment | Electrophoresis treatment and hot-polymerised polyester epoxy powder |
| Surface Finish | Matt Smooth |
| Colour | White (RAL 9001) |
| Width | 600 mm |
| Height | 1450 mm |
| Depth | 260 mm |
| Net Weight | 25 kg |
| Quantity Per Set | Set of 1 |

Environment

| Ip Degree Of Protection | IP55 with door |
|-------------------------|---|
| Ik Degree Of Protection | IK10 with door conforming to EN/IEC 62262 |
| Mechanical Robustness | Seismic tests - 2.5G conforming to IEC 60068-2-57 |

Packing Units

| - | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 12.0 cm |
| Package 1 Width | 65.0 cm |
| Package 1 Length | 147.0 cm |
| Package 1 Weight | 26.0 kg |
| Unit Type Of Package 2 | Р2М |
| Number Of Units In Package 2 | 7 |
| Package 2 Height | 95.0 cm |
| Package 2 Width | 120.0 cm |
| Package 2 Length | 200.0 cm |
| Package 2 Weight | 250.01 kg |

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

Certifications & Standards

| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
|--------------------------|---|
| | EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| | Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |