Product datasheet

Specifications



IP55 PLAIN ROOF W300 D400

08453





Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Roof
Range Compatibility	Prisma Prisma P enclosure
Installation Description	Cubicle duct - width 300 mm, depth 400 mm
Provided Equipment	Quarter-turn fasteners
Type Of Front Cover	Plain

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder	-
Surface Finish	Matt Smooth	
Colour	White (RAL 9001)	
Special Colour Options	Yes	
Width	300 mm	
Depth	400 mm	
Net Weight	1.4 kg	
Quantity Per Set	Set of 1	

Environment

Ip Degree Of Protection	IP55

Packing Units

v	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	31.0 cm
Package 1 Length	41.5 cm
Package 1 Weight	1.4 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	120

Package 2 Height	80.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	168.0 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information