

Product datasheet

Specifications



modular impulse counter CI - 230V

15443

Main

| | |
|---------------------------|--|
| Range | Acti9 |
| Device Short Name | iCI |
| Product Or Component Type | Impulse counter |
| Range Compatibility | Prisma Prisma P door Prisma Prisma G door |
| Type Of Measurement | Impulse number |
| Display Type | Electromechanical 7 digit(s) |
| Maximum Value Measured | 9999999 |

Complementary

| | |
|---------------------------|----------------------|
| Full Scale Display | 9999999 |
| Impulse Duration | 50 ms |
| Time Between 2 Impulse | 50 ms |
| Reset | Without |
| [Us] Rated Supply Voltage | 230 V AC at 50/60 Hz |
| Power Consumption In Va | 0.15 VA |
| Mounting Mode | Fixed |
| Mounting Support | DIN rail |

Environment

| | |
|--------------|-------|
| 9 Mm Pitches | 4 |
| Width | 36 mm |
| Height | 90 mm |
| Depth | 67 mm |

Packing Units

| | |
|------------------------------|--------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.0 cm |
| Package 1 Width | 7.4 cm |
| Package 1 Length | 9.0 cm |
| Package 1 Weight | 93.0 g |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|----------|
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 72 |
| Package 2 Height | 30.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 7.111 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability





Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

| | | |
|---|----------------------------|---|
|  | Reach Free Of Svhc | |
|  | Toxic Heavy Metal Free | |
|  | Mercury Free | |
|  | Rohs Exemption Information | Yes |
| | | |
| Reach Regulation | | REACH Declaration |
| | | |
| Eu Rohs Directive | | Compliant EU RoHS Declaration |
| | | |
| China Rohs Regulation | | China RoHS declaration |
| | | |
| Weee | | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |