

Product datasheet

Specifications



C60 - circuit breaker - C60L - 2P - 12.5A - L curve

26350

 **Discontinued on:** 6 May 2019

 **Discontinued**

Main

Range Of Product	C60
Range	Multi9
Product Name	C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60L
Device Application	Motor
Poles Description	2P
Number Of Protected Poles	2
Neutral Position	Left
[In] Rated Current	12.5 A at 40 °C
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	L
Breaking Capacity	6 kA Icu at 415 V AC 50/60 Hz per pole conforming to EN/IEC 60947-2 20 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 50 kA Icu at 230...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 25 kA Icu at 400...415 V AC 50/60 Hz conforming to EN/IEC 60947-2
Suitability For Isolation	Yes conforming to IEC 60947-2

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	440 V AC 50/60 Hz 230...240 V AC 50/60 Hz 400...415 V AC 50/60 Hz
Magnetic Tripping Limit	12 x In
Limitation Class	3 conforming to EN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	35 mm symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	YES

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

9 Mm Pitches	4
Height	81 mm
Width	36 mm
Depth	73 mm
Net Weight	0.24 kg
Mechanical Durability	20000 cycles
Connections - Terminals	Tunnel type terminals25 mm² flexible Tunnel type terminals35 mm² rigid
Wire Stripping Length	14 mm
Earth-Leakage Protection	Separate block

Environment

Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	3.6 cm
Package 1 Length	7.3 cm
Package 1 Weight	0.239 kg

Contractual warranty

Warranty	18 months
----------	-----------