Product datasheet

Specifications





C60 - earth leakage add-on block -Vigi C60 - 2P - 40A - 30mA

26537

() Discontinued on: 30 Jun 2021

Main

Product Or Component Type	Add-on residual current devices
Device Short Name	Vigi C60
Poles Description	2P
[In] Rated Current	40 A
Network Type	AC
Earth-Leakage Sensitivity	30 mA
Earth-Leakage Protection Time Delay	Instantaneous
Earth-Leakage Protection Class	Туре АС

Complementary

Complementary	
Device Location In System	Outgoer
Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	220415 V AC 50/60 Hz
Residual Current Tripping Technology	Voltage dependent
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-2
Mounting Support	35 mm symmetrical DIN rail
Electrical Connection To Mcb	By screws
9 Mm Pitches	4
Height	87 mm
Width	72 mm
Depth	74 mm
Net Weight	0.12 kg
Mechanical Durability	20000 cycles
Connections - Terminals	Tunnel type terminals 0.525 mm² flexible Tunnel type terminals 0.535 mm² rigid
Wire Stripping Length	14 mm
Tightening Torque	3.5 N.m

Environment

Standards

IEC 60947-2

Pollution Degree	3 conforming to IEC 60947-2
Tropicalisation	2 conforming to IEC 60947-2
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-560 °C
Ambient Air Temperature For Storage	-4070 °C

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile