# **Product datasheet**

Specifications





C60 - earth leakage add-on block - Vigi C60 - 3P - 25A - 300mA

26590

Discontinued on: 19 Dec 2018

① Discontinued

#### Main

Product Or Component Type	Add-on residual current devices
Device Short Name	Vigi C60
Poles Description	3P
[In] Rated Current	25 A
Network Type	AC
Earth-Leakage Sensitivity	300 mA
Earth-Leakage Protection Time Delay	Instantaneous
Earth-Leakage Protection Class	Type AC

## Complementary

Device Location In System	Outgoer
Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	220415 V AC 50/60 Hz
Residual Current Tripping Technology	Voltage dependent
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-2
Mounting Support	35 mm symmetrical DIN rail
Electrical Connection To Mcb	By screws
9 Mm Pitches	6
Height	87 mm
Width	108 mm
Depth	74 mm
Net Weight	0.18 kg
Mechanical Durability	20000 cycles
Connections - Terminals	Tunnel type terminals 0.516 mm² flexible Tunnel type terminals 0.525 mm² rigid
Wire Stripping Length	14 mm
Tightening Torque	2 N.m

### **Environment**

Standards IEC 60947-2

Pollution Degree	3 conforming to IEC 60947-2
Tropicalisation	2 conforming to IEC 60947-2
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-560 °C
Ambient Air Temperature For Storage	-4070 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	9.5 cm
Package 1 Length	14.8 cm
Package 1 Weight	0.214 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins