

Product datasheet

Specifications



Optional vertical connection adapter, ComPacT NS1600/NS2500, 3 poles, fixed, 1600A/2500A, 3 parts

33975

Main

Range Of Product	ComPacT NS630b...1600 new generation ComPacT NS1600b...3200 new generation
Product Or Component Type	Connection adapter
Accessory / Separate Part Category	Connection accessory
Range Compatibility	ComPact ComPact NS630b...1600 ComPact ComPact NS1600b...3200
Poles Description	3P
Mounting Mode	Fixed
[In] Rated Current	1600...2500 A

Complementary

Connection Position	Vertical
Connection Pitch	115 mm
Accessory / Separate Part Category	Spare part for ComPact NS630b...1600

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.100 cm
Package 1 Width	19.700 cm
Package 1 Length	29.700 cm
Package 1 Weight	6.517 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	2
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	13.570 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	16
Package 3 Height	44.000 cm
Package 3 Width	80.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Length	120.000 cm
Package 3 Weight	118.928 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Certifications & Standards

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)