



# Gear motor MCH, fixed MasterPact NW, 440/480VAC 50/60Hz

48215

### Main

<b>Device Short Name</b>	gear motor MCH
Product Or Component Type	Gear motor mechanism MCH
Device Application	Automatic spring charging
Range Compatibility	Masterpact MasterPact NW circuit breaker
Control Type	Motor mechanism
[Uc] Control Circuit Voltage	440480 V AC 50/60 Hz
Circuit Breaker Mounting Mode	Fixed

### Complementary

Maximum Charging Time	4 s
Maximum Power Consumption In Va	180 VA

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	23.0 cm
Package 1 Width	14.0 cm
Package 1 Length	14.0 cm
Package 1 Weight	1.874 kg

## **Contractual warranty**

Warranty	18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information