

Product datasheet

Specifications



Rear connection, Masterpact NW 32/25, 3 pole, drawout mounting, max 3200A rating, horizontal conn. from upside pov

64845

Main

Range Of Product	MasterPact NW UL 489
Product Or Component Type	Rear connection
Accessory / Separate Part Category	Connection accessory
Range Compatibility	Masterpact MasterPact NW MasterPact NW32 circuit breaker Masterpact MasterPact NW MasterPact NW25 circuit breaker
Poles Description	3P
Mounting Mode	Drawout
[In] Rated Current	2500...3200 A

Complementary

Location Of Connection	Rear
Localisation On Device	Upside
Connection Position	Horizontal
Connection Pitch	115 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	8.0 cm
Package 1 Length	20.0 cm
Package 1 Weight	1.7 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability





Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)